

KEN BEDPAN WASHER DISINFECTOR 731

Intelligent Disinfection

- CLEAN, LEAN & GREEN

- ✓ Total disinfection
- ✓ Easy service access
- ✓ Complies with 15883

The BWD 731 has been developed for hospital wards, isolation wards and nursing homes. It is useful for washing and disinfection of bedpans, urine bottles, washing bowls, suction glasses and similar utensils.

It has a compact design with a small physical footprint, and it is environmentally optimised with a low consumption of energy, water and detergents, which leads to low operational costs.

The machine can be supplied as wall-mounted, floor-mounted and as under counter model.

The BWD 731 is easy to operate by touch panel with icons showing all relevant information of the program needed by the operators.

The various bedpan holders are suitable for all types of bedpan. The capacity of the BWD 731 is one bedpan or two urinal bottles. A special utensils basket is available for washing kidney bowls, scissors, bowls and other small items.

All data from the BWD 731 are fully exchangeable with common computer systems.



HEALTHCARE



All KEN machines are in conformity with present EU directives, and all the hospital machines have been constructed in accordance with EN ISO 15883.

Advantages:

Environment

- Low energy costs
- Low water consumption
- Low chemical usage
- Low noise level

User-friendliness

- Easy to use icons
- Quick-start - automatic closing
- Door suitable as slopsink - bedpan emptied automatically

Hygiene safety

- EN 62366 tested
- EN ISO 15883-1-3-5
- Disinfection guarantee

Description	Values
Outer dimensions	H: 855 x W: 450 x D: 555 mm
Outer dimensions with plinth	H: 1150 x W: 450 x D: 555 mm
Dimensions washing chamber	H: 460 x W: 380 x D: 280 mm
Weight excl./incl. packaging	64/82 kg / + plinth 69/87 kg
Built in combitank	10 L
Built in detergent cabinet	1 x 5 L can
Capacity, alternatively-	1 bedpan OR 2 urine bottles OR 1 washing bowl OR 1 utensil basket
Bedpan program	Appr. 7 min
Sealing class	IP 21 (not rinse-proof)
Water connections	Cold: 3/4" G (poss. 1/2" pipe), press: 200-800kPa, temp: 5-30°C, hardness: 0-3°dH Hot: 3/4" G (poss. 1/2" pipe), press: 200-800kPa, temp: 5-70°C, hardness: 0-3°dH
Sound pressure ISO 11204 L	47,5 dB (A)
Water consumption per phase	See technical manual
Power supply options	3N x 200 - 440V AC 50/60Hz + PE+(N) (Single phase available)
Heating elements in combitank	3x2 kW / 3x3 kW
Programs available	5 standard
Drain: Inner ø90 mm, outer ø110 mm	Wall / Floor

Contact a KEN partner

Clean, Lean & Green

KEN HYGIENE SYSTEMS A/S
Bøgebjergvej 60 · DK-5672 Broby
T +45 6263 1091 · F +45 6263 1607
ken@ken.dk · www.ken.dk

Malone Hospital Services Pty Ltd.
24, Tathra Street
West Gosford 2250, NSW
Phone +61 (02) 4323 9731
E-mail: sales@malones.com.au
Internet: www.malones.com.au

